

## Wireless Voice Annunciator - obsolete

The Axis Wireless Voice Annunciator is a programmable output device reproducing voice messages which can be operated by the control panel using its highly flexible and powerful cause and effect programming capabilities.

The activation command is sent from the control panel to the voice annunciator through the AV wireless translator module.

Up to 3 voice messages can be recorded and stored in to the Wireless Voice Annunciator using a dedicated PC application and connecting to the unit through a serial cable. Each message can have a maximum duration of 32 seconds.

The control panel software provides the option of selecting from the 3 different voice messages.

Bi-directional communications with the wireless translator is based on a proven protocol and wireless technology and is fast, reliable and provides the highest level of security.

The wireless communications operates on the frequency of 433MHz.



### Features

- Up to 3 voice messages
- Bi-directional communication protocol between all wireless devices
- Rapid, cost effective installation with minimal disturbance
- Fully Intelligent devices
- Up to 16 wireless Annunciator devices allowed with each translator
- Fully Monitored Primary and Secondary Power Source

### Specification

Operating frequency range	433.05 MHz - 434.79 MHz
Max radiated power	5dBm(3mW)
Radio signal's modulation type	FSK
Operating frequency channels	6
Communication range with 20-VW2W100-ADV Or 20-SGWE100-ADV*	Up to 50m (in open space)
Main battery type	CR123A (3V&1.2Ah)
Secondary battery type	CR123A (3V&1.2Ah)
Main battery lifespan	**5years***
Secondary battery lifespan	**2months***
Temperature range	-10 ° C-+55 ° C
Tolerated humidity range (non condensing)	From 5%RH to 95%RH

Dimensions (HxD)	70x170mm
Weight (without batteries)	410g
IP Rating	20C

## Order Codes and Options

SGVA100/433-ADV: Wireless Voice Annunciator

## Limitations

- \* Ideal operating range: may vary consistently according to environmental conditions.
- \*\* When a low battery condition is indicated, both, main and secondary, batteries must be changed altogether.
- \*\*\* These lifespan values refer to the device being programmed with a control signals transmission period of 12 seconds. If the 20-SGVA100-ADV is activated for 30 seconds a week for test, the primary battery's lifespan reduces to 3 years.

[Check if this document is up to date](#) | [Give us feedback](#)

Advanced, The Bridges, Balliol Business Park, Newcastle upon Tyne, NE12 8EW, UK T: +44 (0)345 894 7000, E: [enquiries@advancedco.com](mailto:enquiries@advancedco.com),  
W: [www.advancedco.com](http://www.advancedco.com)

As our policy is one of constant product improvement the right is therefore reserved to modify product specifications without prior notice.